

# 치과기공물 보세가공에 대한 전망

한국모던치과기공소

## - 서 론 -

가  
가

### ◇ 치과기공물 보세가공은 가능한가 ◇

1970  
1972 [ ]

2)  
가

3)

가

40

가

가

, 1976

2

가  
가

가

4)

가

### ◇ 치과기공물 보세가공의 가능성 ◇

가

가

가

:

가

[ ]

가

가

[ ] 3 Unit Bridge

10 Work Day

5

14

## - 본 론 -

### ◇ 치과기공물 보세가공의 정의 ◇

1) 가  
( : , )

:

가

**RECOMMENDED DENTAL  
LABORATORY TIME  
SCHEDULE  
FOR RELIABLE RESULTS  
AND SATISFACTORY  
SERVICE**

**Working time in laboratory  
( 8 Hour Day )**

	<b>Minimum Days</b>
<b>Model and Bite Blocks</b> .....	3
<b>Trays</b> .....	3
<b>Tracers</b> .....	3
<b>Try In</b> .....	3
<b>Re-Trys</b> .....	2
<b>Finish</b> .....	5
<b>Minor Repairs</b> .....	1
<b>Extensive Repairs should call</b>	
<b>Relines</b> .....	2
<b>Transfers</b> .....	4
<b>Palatal or Lingual</b> .....	6
<b>Wrought bars</b>	
<b>Cast Gold or Chrome</b>	
<b>Partials</b> .....	7
<b>Fixed Bridge</b> .....	8
<b>Direct Inlays</b> .....	2
<b>Indirect Inlays</b> .....	5
<b>Plastic or Porcelain</b> .....	7
<b>Veneer Crowns</b> .....	6
<b>Acrylic Facings</b> .....	5
<b>Acrylic Jackets</b> .....	6
<b>Porcelain Jackets</b> .....	7
<b>Precision Attachments or Special Work should call</b>	

**DIES AND PREPARATORY MODELS**

Dies . . . . . \$4.75 each  
 Bridge model . . . . . 3.50 up  
 Mount models . . . . . 2.25  
 STAT<sup>™</sup> ARTICULATOR

**GOLD STATIONARY BRIDGEWORK\***

Veneer crown casting . . . . . 19.00  
 Veneer crown or pontic with  
 clear incisal . . . . . additional 2.00 per unit  
 Full cast crown . . . . . 22.00  
 Gold saddle veneer style pontic . . . . . 19.00  
 Gold bridgework connections . . . . . 7.00  
 Direct casting . . . . . 7.50  
 Indirect inlays . . . . . 14.00 up

**COPINGS\***

Plastic transfer coping . . . . . 6.00  
 Cast coping . . . . . 7.25  
 Luxene full-coverage coping . . . . . 12.00  
 Gold thimble for porcelain jacket crown . . . . . 17.00  
 Internal core . . . . . 17.00  
 Telescope coping . . . . . 18.00

① Dies Preparatory Models

**JACKET CROWNS**

Porcelain jacket crown with opaque  
 base . . . . . 36.00  
 Aluminous procelain jacket crown . . . . . 38.00  
 Ceramco (alloy additional) . . . . . 47.00  
 Staining and characterizing  
 (per unit) . . . . . 2.00 up

**CERAMIC FIXED BRIDGEWORK**

Ceramco abutments or pontics (full coverage  
 or veneer style)\* . . . . . 47.00  
 Connections . . . . . 9.00

**E-Z-CERAM\* (96% PRECIOUS METAL)**

Casting . . . . . 19.50  
 Porcelain . . . . . 29.50

REHABILITATION RESTORATIONS 5 or more  
 continuous units . . . . . add 3.00 per unit

**ALL PROCELAIN IS VACUUM FIRED  
\*ALLOY ADDITIONAL**

② Jacket Croums

[     ]

[     ]

Die (     )  
 60 (     46,000 )

가



3) 가 ( ) 가 가  
[Paper working] : 가

4) 가 가  
가 (?)  
[ ]

5) 가 가 가  
가 : 가

가 가 가 가  
가 가

◇ 보세가공실현에 현재까지 제기된 문제점 ◇

가 가 가 가  
: 가 가

[Stone] 가 : 가

가 가 가  
[ ] 가

가

가

가

**- 결론 -**

가

◇ 보세가공 수출조합 구성의 필요성 ◇  
가

가

가

가

가